

## Lifteo ELA - Mobile patient lift

### Product short description:

**Lifteo ELA** is a lift with electric adjustment of the base leg spacing and fixed, manual or electric sling.



### Product gallery:



## Product description:

### Lifteo ELA - Mobile patient lift

Easy-to-use lift designed for patients whose weight does not exceed 160 kg. The lift is distinguished by a wide selection of compatible slings. The capacious battery gives the ability to perform about 35 full lifting and lowering cycles on a single charge with a maximum load of 160 kg.

#### Features:

Can be used in small spaces,  
emergency lowering function,  
maximum safety and comfort,  
overload protection,  
very easy to maneuver,  
relieves the strain on the operator's spine during handling,  
ability to drive under a chair, wheelchair or toilet, thanks to the device's swinging legs,  
use of high-quality electrical components,  
electric control for raising, lowering, adjusting the legs and the sling (4ESB-S).

#### Lifteo ELA will be an excellent choice for:

### Hospital

Developed for use in hospitals, the innovative Lifteo ELA mobile patient lift is an indispensable tool to support the patient care process. The use of this advanced device brings numerous benefits to both medical personnel and patients.

### Care home

Lifteo ELA mobile patient lift is an invaluable aid for medical staff and patients in the sanatorium environment. With its advanced features and ergonomic design, it enables effective and safe movement of people with various health needs in rehabilitation therapy.

### Private usage

Lifteo ELA mobile patient lift is an indispensable tool for home use, providing support and safety during daily activities. Thanks to its use, it is possible to effectively and comfortably lift and move people with limited mobility.

### Sanatorium

Lifteo ELA mobile patient lift is an invaluable aid for medical staff and patients in the sanatorium environment. With its advanced features and ergonomic design, it enables effective and safe movement of people with various health needs in rehabilitation therapy.

## Compatible slings:

### Universal

Head support: yesMaterial: polyesterSizes: M, L, XL, bariatricLifting capacity: 318 kg / 454 kgAttachment: loops

### Bath & Toilet

Head support: yesMaterial: polyester meshSizes: M, L, XLLifting capacity: 250 kgAttachment: loops

### Bath & Toilet

Head support: noMaterial: polyester meshSizes: M, L, XLLifting capacity: 250 kgAttachment: clips

## Technical data:

|                                               |                                                                                                                                                                                                          |
|-----------------------------------------------|----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Base legs spreading:                          | electrical                                                                                                                                                                                               |
| Max. safe working load (SWL)[kg]:             | 160 (120)*                                                                                                                                                                                               |
| Length [cm]:                                  | 128                                                                                                                                                                                                      |
| Width [cm]:                                   | 61                                                                                                                                                                                                       |
| Height [cm]:                                  | 136                                                                                                                                                                                                      |
| Lifting range [cm]:                           | 72 - 194                                                                                                                                                                                                 |
| Min. turning diameter [cm]:                   | 140                                                                                                                                                                                                      |
| Min. base legs width (int./ext.) [cm]:        | 49/61                                                                                                                                                                                                    |
| Max. base legs width (int./ext.) [cm]:        | 100/112                                                                                                                                                                                                  |
| Base legs height [cm]:                        | 9,5                                                                                                                                                                                                      |
| Wheels diameter (without/with lock) [cm]:     | 7,5/10                                                                                                                                                                                                   |
| Weight [kg]:                                  | 45                                                                                                                                                                                                       |
| Battery capacity [Ah]:                        | 2,9                                                                                                                                                                                                      |
| Charger (integrated with control box) [V/Hz]: | 100-240 / 50-60 (no integrated)                                                                                                                                                                          |
| Remote control functions:                     | <ul style="list-style-type: none"> <li>• up/down</li> <li>• electric leg spread: outside / inside</li> <li>• overload indicator</li> <li>• battery charge status</li> <li>• service indicator</li> </ul> |
| Lifting speed (raising/lowering) [s]:         | 34 / 33                                                                                                                                                                                                  |
| Packed dimensions (L x W x H) [cm]:           | 150 x 80 x 62                                                                                                                                                                                            |

## Video presentation:

## Product codes:

Reference: 01-WPP-0107-002

EAN13: -

UPC: -

## Product features:

## Product attributes: